

Specification Sheet

Part Number: 156-01714



LOC Locking Clamp, 20–25 mm, with T50SMVC Swivel Tie, PA66HIRHSUV, Black, 1000/ctn

Article Number	156-01714
Type	T50SMVCLOC20-25
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">•Bundle can rotate to any orientation, allowing routing in any direction regardless of mounting point.•Clip is reusable, making relocation or adjustments simple.•All-in-one bundling and mounting solution reduces costs.
Quantity Per	carton
Product Description	HellermannTyton's 1-Piece Cable Tie with Pipe Clip secures cables to tubular frame rails. The cable tie bundles wires, cables or tubes, and the C-clip snaps onto the tubular frame rail. The clip can be removed from the mounting surface and reinstalled without additional fasteners.
Short Description	LOC Locking Clamp, 20–25 mm, with T50SMVC Swivel Tie, PA66HIRHSUV, Black, 1000/ctn

Global Part Name

T50SMVCLOC20-25-PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial)

50

Minimum Tensile Strength (Metric)

225

Length L (Imperial)

8.3

Length L (Metric)

210.0

Fixation Method

Omega Clips

Identification Plate Position

none

Width W (Metric)

12.0

Bundle Diameter Min (Imperial)

0.79

Bundle Diameter Min (Metric)

50.0

Bundle Diameter Max (Imperial)

2.0

Bundle Diameter Max (Metric)

50.0

Height H (Imperial)

1.53

Height H (Metric)

38.9

Depth D (imperial)

0.47

Depth D (metric)

12.0

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Material Cable Tie	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Flammability	UL 94 HB
Halogen free	Yes
Operating Temperature (Metric)	-40°F to +230°F (-40°C to +110°C)
ROHS Complaint	Yes
Package Quantity(Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988
Weight (Metric)	3.84
Weight (Imperial)	0.14