

Specification Sheet

Part Number: 156-01781



MOC Clip, 26 mm, Assembled to T50SMVC Swivel Tie, PA66HIRHSUV, Black, 1000/ctn

Article Number	156-01781
Type	T50SMVCMOC26M
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">• Patented retention design on clip features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement.• Controlled flex and angled entry promote easy installation.• Independent rotation allows for adjustable routing orientation.• Cable tie accommodates wide range of secondary bundle sizes.
Quantity Per	carton

Product Description

The MOC to Swivel Tie is a rotatable routing clip coupled to a cable tie that keeps two routings secured and separated. Tie provides additional security against axial slip by clamping around solid tube, pipe or harness. The swivel coupler allows the two routings to rotate independently of each other.

Short Description

MOC Clip, 26 mm, Assembled to T50SMVC Swivel Tie, PA66HIRHSUV, Black, 1000/ctn

Global Part Name

T50SMVCMOC26M-PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial)

50

Minimum Tensile Strength (Metric)

225

Length L (Imperial)

1.61

Length L (Metric)

41.0

Fixation Method

Omega Clips

Identification Plate Position

none

Bundle Diameter Min (Imperial)

0.91

Bundle Diameter Min (Metric)

23.0

Bundle Diameter Max (Imperial)

1.14

Bundle Diameter Max (Metric)

29.0

Height H (Imperial)

2.09

Height H (Metric)

53.0

Depth D (imperial)

0.47

Depth D (metric)

12.0

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen free	Yes
Operating Temperature (Metric)	-40°F to +230°F (-40°C to +110°C)
ROHS Complaint	Yes
Package Quantity(Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988
Weight (Metric)	4.15
Weight (Imperial)	0.15