

## Specification Sheet

Part Number: 156-01815



MOC Clip, 10 mm, Unassembled to T50R Tie, PA66HIRHSUV, Black, 1000/ctn

Article Number	156-01815
Type	T50RMOC10SAD-SET
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none"><li>• Patented retention design on clip features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement.</li><li>• Controlled flex and angled entry promote easy installation.</li><li>• Fixed connector controls routing orientation.</li><li>• Cable tie accommodates wide range of secondary bundle sizes.</li></ul>
Quantity Per	carton

### Product Description

The MOC with Saddle to T50R Tie has a two-piece design that keeps two routings secured together while providing a fixed orientation for each bundle. The bi-directional saddle design allows the bundles to be coupled parallel or perpendicular to one another. Tie provides additional security against axial slip by clamping around solid tube, pipe or harness.

<b>Short Description</b>	MOC Clip, 10 mm, Unassembled to T50R Tie, PA66HIRHSUV, Black, 1000/ctn
<b>Global Part Name</b>	T50RMOC10SAD-SET-PA66HIRHSUV-BK
<b>Minimum Tensile Strength (Imperial)</b>	50
<b>Minimum Tensile Strength (Metric)</b>	225
<b>Length L (Imperial)</b>	0.67
<b>Length L (Metric)</b>	16.9
<b>Fixation Method</b>	Omega Clips
<b>Identification Plate Position</b>	none
<b>Releasable Closure</b>	No
<b>Tie Closure</b>	plastic pawl
<b>Variant</b>	Inside Serrated
<b>Bundle Diameter Min (Imperial)</b>	0.37
<b>Bundle Diameter Min (Metric)</b>	9.5
<b>Bundle Diameter Max (Imperial)</b>	0.45
<b>Bundle Diameter Max (Metric)</b>	11.5
<b>Height H (Imperial)</b>	1.02
<b>Height H (Metric)</b>	25.8

**Depth D (imperial)** 0.39

**Depth D (metric)** 10.0

**Material** Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

**Material Shortcut** PA66HIRHSUV

**Flammability** UL 94 HB

**Halogen free** Yes

**Operating Temperature (Metric)** -40°F to +230°F (-40°C to +110°C)

**ROHS Complaint** Yes

**Package Quantity(Imperial)** 1000

**Package Quantity (Metric)** 1000

**Customs Number** 3926909988

**Weight (Metric)** 1.34

**Weight (Imperial)** 0.05

