

Specification Sheet

Part Number: 156-01821



MOC Clip, 26 mm, Unassembled to T50R Tie, PA66HIRHSUV, Black, 1000/ctn

Article Number	156-01821
Type	T50RMOC26SAD-SET
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">• Patented retention design on clip features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement.• Controlled flex and angled entry promote easy installation.• Fixed connector controls routing orientation.• Cable tie accommodates wide range of secondary bundle sizes.
Quantity Per	carton

Product Description

The MOC with Saddle to T50R Tie has a two-piece design that keeps two routings secured together while providing a fixed orientation for each bundle. The bi-directional saddle design allows the bundles to be coupled parallel or perpendicular to one another. Tie provides additional security against axial slip by clamping around solid tube, pipe or harness.

Short Description	MOC Clip, 26 mm, Unassembled to T50R Tie, PA66HIRHSUV, Black, 1000/ctn
Global Part Name	T50RMOC26SAD-SET-PA66HIRHSUV-BK
Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	1.36
Length L (Metric)	34.5
Fixation Method	Omega Clips
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Bundle Diameter Min (Imperial)	0.91
Bundle Diameter Min (Metric)	23.0
Bundle Diameter Max (Imperial)	1.14
Bundle Diameter Max (Metric)	29.0
Height H (Imperial)	1.85
Height H (Metric)	47.1

Depth D (imperial) 0.47

Depth D (metric) 12.0

Material Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

Material Shortcut PA66HIRHSUV

Flammability UL 94 HB

Halogen free Yes

Operating Temperature (Metric) -40°F to +230°F (-40°C to +110°C)

ROHS Complaint Yes

Package Quantity(Imperial) 1000

Package Quantity (Metric) 1000

Customs Number 3926909988

Weight (Metric) 4.15

Weight (Imperial) 0.15

