

## Specification Sheet

Part Number: 156-01837



**Article Number**

156-01837

**Type**

MOC10LOC5-9

**Color**

Black (BK)

**Features & Benefits**

- Patented retention design of clip features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement.
- Clip and clamp both offer easy bundle installation.
- Independent rotation allows for adjustable routing orientation.
- Locking clamp dynamically fits a range of bundle sizes.

**Quantity Per**

carton

**Product Description**

The MOC to LOC is a rotatable dual routing clip and clamp combination that keeps two routings secured and separated. A swivel coupler allows them to rotate independently of each other.

**Short Description**

LOC Locking Clamp, 5-9 mm, to MOC Clip, 10 mm, PA66HIRHSUV, Black, 1000/ctn

Global Part Name

MOC10LOC5-9-PA66HIRHSUV-BK

Length L (Imperial)

1.63

Length L (Metric)

41.30

Variant

Clip to Clamp

Bundle Diameter Min (Imperial)

0.37

Bundle Diameter Min (Metric)

9.5

Bundle Diameter Max (Imperial)

0.45

Bundle Diameter Max (Metric)

11.5

Height H (Imperial)

0.93

Height H (Metric)

23.6

Depth D (imperial)

0.47

Depth D (metric)

12.0

Material

Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

Material Shortcut

PA66HIRHSUV

Flammability

UL 94 HB

**Halogen free** Yes

**Operating Temperature (Metric)** -40°F to +230°F (-40°C to +110°C)

**ROHS Complaint** Yes

**Package Quantity(Imperial)** 1000

**Package Quantity (Metric)** 1000

**Customs Number** 3926909988

**Weight (Metric)** 3.36

**Weight (Imperial)** 0.12