

Specification Sheet

Part Number: 156-01853



LOC Locking Clamp, 10-14 mm, to MOC Clip, 6 mm, PA66HIRHSUV, Black, 1000/ctn

Article Number	156-01853
Type	MOC6LOC10-14
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">• Patented retention design of clip features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement.• Clip and clamp both offer easy bundle installation.• Independent rotation allows for adjustable routing orientation.• Locking clamp dynamically fits a range of bundle sizes.
Quantity Per	carton

Product Description

The MOC to LOC is a rotatable dual routing clip and clamp combination that keeps two routings secured and separated. A swivel coupler allows them to rotate independently of each other.

Short Description	LOC Locking Clamp, 10-14 mm, to MOC Clip, 6 mm, PA66HIRHSUV, Black, 1000/ctn
Global Part Name	MOC6LOC10-14-PA66HIRHSUV-BK
Length L (Imperial)	1.59
Length L (Metric)	40.40
Variant	Clip to Clamp
Bundle Diameter Min (Imperial)	0.22
Bundle Diameter Min (Metric)	5.5
Bundle Diameter Max (Imperial)	0.27
Bundle Diameter Max (Metric)	6.8
Height H (Imperial)	1.08
Height H (Metric)	27.4
Depth D (imperial)	0.47
Depth D (metric)	12.0
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV

Flammability	UL 94 HB
Halogen free	Yes
Operating Temperature (Metric)	-40°F to +230°F (-40°C to +110°C)
ROHS Complaint	Yes
Package Quantity(Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988
Weight (Metric)	3.389999999999997
Weight (Imperial)	0.12