

Specification Sheet

Part Number: 156-01859



LOC Locking Clamp, 10-14 mm, to MOC Clip, 9 mm, PA66HIRHSUV, Black, 1000/ctn

Article Number

156-01859

Type

MOC9LOC10-14

Color

Black (BK)

Features & Benefits

- Patented retention design of clip features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement.
- Clip and clamp both offer easy bundle installation.
- Independent rotation allows for adjustable routing orientation.
- Locking clamp dynamically fits a range of bundle sizes.

Quantity Per

carton

Product Description

The MOC to LOC is a rotatable dual routing clip and clamp combination that keeps two routings secured and separated. A swivel coupler allows them to rotate independently of each other.

Short Description	LOC Locking Clamp, 10-14 mm, to MOC Clip, 9 mm, PA66HIRHSUV, Black, 1000/ctn
Global Part Name	MOC9LOC10-14-PA66HIRHSUV-BK
Length L (Imperial)	1.72
Length L (Metric)	43.70
Variant	Clip to Clamp
Bundle Diameter Min (Imperial)	0.31
Bundle Diameter Min (Metric)	8.0
Bundle Diameter Max (Imperial)	0.39
Bundle Diameter Max (Metric)	10.0
Height H (Imperial)	1.08
Height H (Metric)	27.4
Depth D (imperial)	0.47
Depth D (metric)	12.0
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV

Flammability	UL 94 HB
Halogen free	Yes
Operating Temperature (Metric)	-40°F to +230°F (-40°C to +110°C)
ROHS Complaint	Yes
Package Quantity(Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988
Weight (Metric)	3.7399999999999998
Weight (Imperial)	0.13