

## Specification Sheet

Part Number: 156-01865



LOC Locking Clamp, 10-14 mm, to MOC Clip, 14 mm, PA66HIRHSUV, Black, 1000/ctn

**Article Number**

156-01865

**Type**

MOC14LOC10-14

**Color**

Black (BK)

**Features & Benefits**

- Patented retention design of clip features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement.
- Clip and clamp both offer easy bundle installation.
- Independent rotation allows for adjustable routing orientation.
- Locking clamp dynamically fits a range of bundle sizes.

**Quantity Per**

carton

**Product Description**

The MOC to LOC is a rotatable dual routing clip and clamp combination that keeps two routings secured and separated. A swivel coupler allows them to rotate independently of each other.

<b>Short Description</b>	LOC Locking Clamp, 10-14 mm, to MOC Clip, 14 mm, PA66HIRHSUV, Black, 1000/ctn
<b>Global Part Name</b>	MOC14LOC10-14-PA66HIRHSUV-BK
<b>Length L (Imperial)</b>	1.94
<b>Length L (Metric)</b>	49.20
<b>Variant</b>	Clip to Clamp
<b>Bundle Diameter Min (Imperial)</b>	0.51
<b>Bundle Diameter Min (Metric)</b>	13.0
<b>Bundle Diameter Max (Imperial)</b>	0.62
<b>Bundle Diameter Max (Metric)</b>	15.8
<b>Height H (Imperial)</b>	1.08
<b>Height H (Metric)</b>	27.4
<b>Depth D (imperial)</b>	0.47
<b>Depth D (metric)</b>	12.0
<b>Material</b>	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
<b>Material Shortcut</b>	PA66HIRHSUV

<b>Flammability</b>	UL 94 HB
<b>Halogen free</b>	Yes
<b>Operating Temperature (Metric)</b>	-40°F to +230°F (-40°C to +110°C)
<b>ROHS Complaint</b>	Yes
<b>Package Quantity(Imperial)</b>	1000
<b>Package Quantity (Metric)</b>	1000
<b>Customs Number</b>	3926909988
<b>Weight (Metric)</b>	4.39
<b>Weight (Imperial)</b>	0.15