

Specification Sheet

Part Number: 156-01885



LOC Locking Clamp, 15-19 mm, to MOC Clip, 10 mm, PA66HIRHSUV, Black, 1000/ctn

Article Number

156-01885

Type

MOC10LOC15-19

Color

Black (BK)

Features & Benefits

- Patented retention design of clip features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement.
- Clip and clamp both offer easy bundle installation.
- Independent rotation allows for adjustable routing orientation.
- Locking clamp dynamically fits a range of bundle sizes.

Quantity Per

carton

Product Description

The MOC to LOC is a rotatable dual routing clip and clamp combination that keeps two routings secured and separated. A swivel coupler allows them to rotate independently of each other.

Short Description

LOC Locking Clamp, 15-19 mm, to MOC Clip, 10 mm, PA66HIRHSUV, Black, 1000/ctn

Global Part Name

MOC10LOC15-19-PA66HIRHSUV-BK

Length L (Imperial)

1.81

Length L (Metric)

46.10

Variant

Clip to Clamp

Bundle Diameter Min (Imperial)

0.37

Bundle Diameter Min (Metric)

9.5

Bundle Diameter Max (Imperial)

0.45

Bundle Diameter Max (Metric)

11.5

Height H (Imperial)

1.31

Height H (Metric)

33.4

Depth D (imperial)

0.47

Depth D (metric)

12.0

Material

Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

Material Shortcut

PA66HIRHSUV

Flammability	UL 94 HB
Halogen free	Yes
Operating Temperature (Metric)	-40°F to +230°F (-40°C to +110°C)
ROHS Complaint	Yes
Package Quantity(Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988
Weight (Metric)	4.37
Weight (Imperial)	0.15