

## Specification Sheet

Part Number: 156-01887



LOC Locking Clamp, 15-19 mm, to MOC Clip, 12 mm, PA66HIRHSUV, Black, 1000/ctn

Article Number	156-01887
Type	MOC12LOC15-19
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none"><li>• Patented retention design of clip features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement.</li><li>• Clip and clamp both offer easy bundle installation.</li><li>• Independent rotation allows for adjustable routing orientation.</li><li>• Locking clamp dynamically fits a range of bundle sizes.</li></ul>
Quantity Per	carton

### Product Description

The MOC to LOC is a rotatable dual routing clip and clamp combination that keeps two routings secured and separated. A swivel coupler allows them to rotate independently of each other.

**Short Description**

LOC Locking Clamp, 15-19 mm, to MOC Clip, 12 mm, PA66HIRHSUV, Black, 1000/ctn

**Global Part Name**

MOC12LOC15-19-PA66HIRHSUV-BK

**Length L (Imperial)**

1.89

**Length L (Metric)**

48.00

**Variant**

Clip to Clamp

**Bundle Diameter Min (Imperial)**

0.41

**Bundle Diameter Min (Metric)**

10.5

**Bundle Diameter Max (Imperial)**

0.54

**Bundle Diameter Max (Metric)**

13.8

**Height H (Imperial)**

1.31

**Height H (Metric)**

33.4

**Depth D (imperial)**

0.47

**Depth D (metric)**

12.0

**Material**

Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

**Material Shortcut**

PA66HIRHSUV

<b>Flammability</b>	UL 94 HB
<b>Halogen free</b>	Yes
<b>Operating Temperature (Metric)</b>	-40°F to +230°F (-40°C to +110°C)
<b>ROHS Complaint</b>	Yes
<b>Package Quantity(Imperial)</b>	1000
<b>Package Quantity (Metric)</b>	1000
<b>Customs Number</b>	3926909988
<b>Weight (Metric)</b>	4.62
<b>Weight (Imperial)</b>	0.16