

## Specification Sheet

Part Number: 156-01889



LOC Locking Clamp, 15-19 mm, to MOC Clip, 14 mm, PA66HIRHSUV, Black, 1000/ctn

**Article Number**

156-01889

**Type**

MOC14LOC15-19

**Color**

Black (BK)

**Features & Benefits**

- Patented retention design of clip features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement.
- Clip and clamp both offer easy bundle installation.
- Independent rotation allows for adjustable routing orientation.
- Locking clamp dynamically fits a range of bundle sizes.

**Quantity Per**

carton

**Product Description**

The MOC to LOC is a rotatable dual routing clip and clamp combination that keeps two routings secured and separated. A swivel coupler allows them to rotate independently of each other.

**Short Description**

LOC Locking Clamp, 15-19 mm, to MOC Clip, 14 mm, PA66HIRHSUV, Black, 1000/ctn

**Global Part Name**

MOC14LOC15-19-PA66HIRHSUV-BK

**Length L (Imperial)**

1.96

**Length L (Metric)**

49.90

**Variant**

Clip to Clamp

**Bundle Diameter Min (Imperial)**

0.51

**Bundle Diameter Min (Metric)**

13.0

**Bundle Diameter Max (Imperial)**

0.62

**Bundle Diameter Max (Metric)**

15.8

**Height H (Imperial)**

1.31

**Height H (Metric)**

33.4

**Depth D (imperial)**

0.47

**Depth D (metric)**

12.0

**Material**

Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

**Material Shortcut**

PA66HIRHSUV

<b>Flammability</b>	UL 94 HB
<b>Halogen free</b>	Yes
<b>Operating Temperature (Metric)</b>	-40°F to +230°F (-40°C to +110°C)
<b>ROHS Complaint</b>	Yes
<b>Package Quantity(Imperial)</b>	1000
<b>Package Quantity (Metric)</b>	1000
<b>Customs Number</b>	3926909988
<b>Weight (Metric)</b>	4.8100000000000005
<b>Weight (Imperial)</b>	0.17