

Specification Sheet

Part Number: 156-01897



LOC Locking Clamp, 15-19 mm, to MOC Clip, 26 mm, PA66HIRHSUV, Black, 1000/ctn

Article Number

156-01897

Type

MOC26LOC15-19

Color

Black (BK)

Features & Benefits

- Patented retention design of clip features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement.
- Clip and clamp both offer easy bundle installation.
- Independent rotation allows for adjustable routing orientation.
- Locking clamp dynamically fits a range of bundle sizes.

Quantity Per

carton

Product Description

The MOC to LOC is a rotatable dual routing clip and clamp combination that keeps two routings secured and separated. A swivel coupler allows them to rotate independently of each other.

Short Description	LOC Locking Clamp, 15-19 mm, to MOC Clip, 26 mm, PA66HIRHSUV, Black, 1000/ctn
Global Part Name	MOC26LOC15-19-PA66HIRHSUV-BK
Length L (Imperial)	2.52
Length L (Metric)	63.90
Variant	Clip to Clamp
Bundle Diameter Min (Imperial)	0.91
Bundle Diameter Min (Metric)	23.0
Bundle Diameter Max (Imperial)	1.14
Bundle Diameter Max (Metric)	29.0
Height H (Imperial)	1.61
Height H (Metric)	41.0
Depth D (imperial)	0.47
Depth D (metric)	12.0
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV

Flammability	UL 94 HB
Halogen free	Yes
Operating Temperature (Metric)	-40°F to +230°F (-40°C to +110°C)
ROHS Complaint	Yes
Package Quantity(Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988
Weight (Metric)	7.460000000000001
Weight (Imperial)	0.26