

Specification Sheet

Part Number: 156-01975



MOC Clip to MOC Clip Perpendicular, 7 mm, 8 mm Perpendicular, PA66HIRHSUV, Black, 1000/ctn

Article Number

156-01975

Type

MOC7FMOC8M180

Color

Black (BK)

Features & Benefits

- Patented retention design features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement.
- Controlled flex and angled entry promote easy installation.
- Independent rotation allows for adjustable routing orientation.

Quantity Per

carton

Product Description

The MOC to MOC 180 is a rotatable dual routing clip that keeps two routings secured and separated. One clip is orientated 90 degrees from the other to provide alternative access for bundle attachment. A swivel coupler allows them to rotate independently of each other.

| | |
|---------------------------------------|--|
| Short Description | MOC Clip to MOC Clip Perpendicular, 7 mm, 8 mm Perpendicular, PA66HIRHSUV, Black, 1000/ctn |
| Global Part Name | MOC7FMOC8M180-PA66HIRHSUV-BK |
| Length L (Imperial) | 1.27 |
| Length L (Metric) | 32.23 |
| Variant | Clip to Clip Transverse |
| Bundle Diameter Min (Imperial) | 0.28 |
| Bundle Diameter Min (Metric) | 7.0 |
| Bundle Diameter Max (Imperial) | 0.35 |
| Bundle Diameter Max (Metric) | 9.0 |
| Height H (Imperial) | 0.53 |
| Height H (Metric) | 13.4 |
| Depth D (imperial) | 0.39 |
| Depth D (metric) | 10.0 |
| Material | Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV) |
| Material Shortcut | PA66HIRHSUV |

| | |
|---------------------------------------|-----------------------------------|
| Flammability | UL 94 HB |
| Halogen free | Yes |
| Operating Temperature (Metric) | -40°F to +230°F (-40°C to +110°C) |
| ROHS Complaint | Yes |
| Package Quantity(Imperial) | 1000 |
| Package Quantity (Metric) | 1000 |
| Customs Number | 3926909988 |
| Weight (Metric) | 1.37 |
| Weight (Imperial) | 0.05 |