

Specification Sheet

Part Number: 156-01976



MOC Clip to MOC Clip Perpendicular, 7 mm, 9 mm Perpendicular, PA66HIRHSUV, Black, 1000/ctn

Article Number

156-01976

Type

MOC7FMOC9M180

Color

Black (BK)

Features & Benefits

- Patented retention design features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement.
- Controlled flex and angled entry promote easy installation.
- Independent rotation allows for adjustable routing orientation.

Quantity Per

carton

Product Description

The MOC to MOC 180 is a rotatable dual routing clip that keeps two routings secured and separated. One clip is orientated 90 degrees from the other to provide alternative access for bundle attachment. A swivel coupler allows them to rotate independently of each other.

Short Description	MOC Clip to MOC Clip Perpendicular, 7 mm, 9 mm Perpendicular, PA66HIRHSUV, Black, 1000/ctn
Global Part Name	MOC7FMOC9M180-PA66HIRHSUV-BK
Length L (Imperial)	1.35
Length L (Metric)	34.24
Variant	Clip to Clip Transverse
Bundle Diameter Min (Imperial)	0.24
Bundle Diameter Min (Metric)	6.0
Bundle Diameter Max (Imperial)	0.31
Bundle Diameter Max (Metric)	8.0
Height H (Imperial)	0.59
Height H (Metric)	15.0
Depth D (imperial)	0.39
Depth D (metric)	10.0
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV

Flammability	UL 94 HB
Halogen free	Yes
Operating Temperature (Metric)	-40°F to +230°F (-40°C to +110°C)
ROHS Complaint	Yes
Package Quantity(Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988
Weight (Metric)	1.54
Weight (Imperial)	0.05