

## Specification Sheet

Part Number: 156-01980



MOC Clip to MOC Clip Perpendicular, 7 mm, 16 mm Perpendicular, PA66HIRHSUV, Black, 1000/ctn

Article Number	156-01980
Type	MOC7FMOC16M180
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none"><li>• Patented retention design features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement.</li><li>• Controlled flex and angled entry promote easy installation.</li><li>• Independent rotation allows for adjustable routing orientation.</li></ul>
Quantity Per	carton

### Product Description

The MOC to MOC 180 is a rotatable dual routing clip that keeps two routings secured and separated. One clip is orientated 90 degrees from the other to provide alternative access for bundle attachment. A swivel coupler allows them to rotate independently of each other.

<b>Short Description</b>	MOC Clip to MOC Clip Perpendicular, 7 mm, 16 mm Perpendicular, PA66HIRHSUV, Black, 1000/ctn
<b>Global Part Name</b>	MOC7FMOC16M180-PA66HIRHSUV-BK
<b>Length L (Imperial)</b>	1.69
<b>Length L (Metric)</b>	42.8
<b>Variant</b>	Clip to Clip Transverse
<b>Bundle Diameter Min (Imperial)</b>	0.24
<b>Bundle Diameter Min (Metric)</b>	6.0
<b>Bundle Diameter Max (Imperial)</b>	0.31
<b>Bundle Diameter Max (Metric)</b>	8.0
<b>Height H (Imperial)</b>	0.90
<b>Height H (Metric)</b>	22.9
<b>Depth D (imperial)</b>	0.47
<b>Depth D (metric)</b>	12.0
<b>Material</b>	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
<b>Material Shortcut</b>	PA66HIRHSUV

<b>Flammability</b>	UL 94 HB
<b>Halogen free</b>	Yes
<b>Operating Temperature (Metric)</b>	-40°F to +230°F (-40°C to +110°C)
<b>ROHS Complaint</b>	Yes
<b>Package Quantity(Imperial)</b>	1000
<b>Package Quantity (Metric)</b>	1000
<b>Customs Number</b>	3926909988
<b>Weight (Metric)</b>	2.53
<b>Weight (Imperial)</b>	0.09