

## Specification Sheet

Part Number: 156-02084



MOC Clip to MOC Clip Perpendicular, 12 mm, 10 mm Perpendicular, PA66HIRHSUV, Black, 1000/ctn

Article Number	156-02084
Type	MOC12FMOC10M180
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none"><li>• Patented retention design features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement.</li><li>• Controlled flex and angled entry promote easy installation.</li><li>• Independent rotation allows for adjustable routing orientation.</li></ul>
Quantity Per	carton
Product Description	The MOC to MOC 180 is a rotatable dual routing clip that keeps two routings secured and separated. One clip is orientated 90 degrees from the other to provide alternative access for bundle attachment. A swivel coupler allows them to rotate independently of each other.

<b>Short Description</b>	MOC Clip to MOC Clip Perpendicular, 12 mm, 10 mm Perpendicular, PA66HIRHSUV, Black, 1000/ctn
<b>Global Part Name</b>	MOC12FMOC10M180-PA66HIRHSUV-BK
<b>Length L (Imperial)</b>	1.68
<b>Length L (Metric)</b>	42.62
<b>Variant</b>	Clip to Clip Transverse
<b>Bundle Diameter Min (Imperial)</b>	0.41
<b>Bundle Diameter Min (Metric)</b>	10.5
<b>Bundle Diameter Max (Imperial)</b>	0.54
<b>Bundle Diameter Max (Metric)</b>	13.8
<b>Height H (Imperial)</b>	0.87
<b>Height H (Metric)</b>	22.1
<b>Depth D (imperial)</b>	0.39
<b>Depth D (metric)</b>	10.0
<b>Material</b>	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
<b>Material Shortcut</b>	PA66HIRHSUV

<b>Flammability</b>	UL 94 HB
<b>Halogen free</b>	Yes
<b>Operating Temperature (Metric)</b>	-40°F to +230°F (-40°C to +110°C)
<b>ROHS Complaint</b>	Yes
<b>Package Quantity(Imperial)</b>	1000
<b>Package Quantity (Metric)</b>	1000
<b>Customs Number</b>	3926909988
<b>Weight (Metric)</b>	2.53
<b>Weight (Imperial)</b>	0.09