

Specification Sheet

Part Number: 156-02153



MOC Clip to MOC Clip Perpendicular, 19 mm, 7 mm Perpendicular, PA66HIRHSUV, Black, 1000/ctn

Article Number	156-02153
Type	MOC19FMOC7M180
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">• Patented retention design features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement.• Controlled flex and angled entry promote easy installation.• Independent rotation allows for adjustable routing orientation.
Quantity Per	carton

Product Description

The MOC to MOC 180 is a rotatable dual routing clip that keeps two routings secured and separated. One clip is orientated 90 degrees from the other to provide alternative access for bundle attachment. A swivel coupler allows them to rotate independently of each other.

Short Description	MOC Clip to MOC Clip Perpendicular, 19 mm, 7 mm Perpendicular, PA66HIRHSUV, Black, 1000/ctn
Global Part Name	MOC19FMOC7M180-PA66HIRHSUV-BK
Length L (Imperial)	1.77
Length L (Metric)	44.84
Variant	Clip to Clip Transverse
Bundle Diameter Min (Imperial)	0.67
Bundle Diameter Min (Metric)	17.0
Bundle Diameter Max (Imperial)	0.86
Bundle Diameter Max (Metric)	21.8
Height H (Imperial)	1.29
Height H (Metric)	32.8
Depth D (imperial)	0.47
Depth D (metric)	12.0
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV

Flammability	UL 94 HB
Halogen free	Yes
Operating Temperature (Metric)	-40°F to +230°F (-40°C to +110°C)
ROHS Complaint	Yes
Package Quantity(Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988
Weight (Metric)	3.6
Weight (Imperial)	0.13