

## Specification Sheet

Part Number: 156-02160



**Article Number**

156-02160

**Type**

MOC19FMOC19M180

**Color**

Black (BK)

**Features & Benefits**

- Patented retention design features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement.
- Controlled flex and angled entry promote easy installation.
- Independent rotation allows for adjustable routing orientation.

**Quantity Per**

carton

**Product Description**

The MOC to MOC 180 is a rotatable dual routing clip that keeps two routings secured and separated. One clip is orientated 90 degrees from the other to provide alternative access for bundle attachment. A swivel coupler allows them to rotate independently of each other.

**Short Description**

MOC Clip to MOC Clip Perpendicular, 19 mm, 19 mm Perpendicular, PA66HIRHSUV, Black, 1000/ctn

Global Part Name

MOC19FMOC19M180-PA66HIRHSUV-BK

Length L (Imperial)

2.54

Length L (Metric)

64.50

Variant

Clip to Clip Transverse

Bundle Diameter Min (Imperial)

0.67

Bundle Diameter Min (Metric)

17.0

Bundle Diameter Max (Imperial)

0.86

Bundle Diameter Max (Metric)

21.8

Height H (Imperial)

1.29

Height H (Metric)

32.8

Depth D (imperial)

0.47

Depth D (metric)

12.0

Material

Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

Material Shortcut

PA66HIRHSUV

Flammability

UL 94 HB

**Halogen free** Yes

**Operating Temperature (Metric)** -40°F to +230°F (-40°C to +110°C)

**ROHS Complaint** Yes

**Package Quantity(Imperial)** 1000

**Package Quantity (Metric)** 1000

**Customs Number** 3926909988

**Weight (Metric)** 6.12

**Weight (Imperial)** 0.22