

## Specification Sheet

Part Number: 156-02226



2-Piece Cable Tie & Edge Clip, 8.0" Long, EC5A, 1–3 mm Panel, 50lb, PA66HIRHSUV/PA66HIRHSUVR5, Bk, 100/pkg

Article Number	156-02226
Type	T50REC5A
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none"><li>•Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole.</li><li>•Edge Clip provides low insertion force and high extraction force ideal for assembly environments.</li></ul>
Quantity Per	bag

### Product Description

HellermannTyton's Two Piece Edge Clip with Cable Tie Assemblies are designed specifically to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. The clip is easy to secure and the extraction force is high due to the integrated metal clamp that holds the edge clip in place.

**Short Description**

2-Piece Cable Tie &amp; Edge Clip, 8.0" Long, EC5A, 1–3 mm Panel, 50lb, PA66HIRHSUV/PA66HIRHSUVR5, Bk, 100/pkg

**Global Part Name**

T50REC5A-PA66HIRHSUVR5/PA66HIRHSUV-BK

**Minimum Tensile Strength (Imperial)**

50.0

**Minimum Tensile Strength (Metric)**

225

**Length L (Imperial)**

8.0

**Length L (Metric)**

203.2

**Fixation Method**

EdgeClip, sideways, assembled, 2 piece

**Identification Plate Position**

none

**Variant**

Inside Serrated

**Width W (Imperial)**

0.18

**Width W (Metric)**

4.6

**Bundle Diameter Min (Imperial)**

0.20

**Bundle Diameter Min (Metric)**

5.0

**Bundle Diameter Max (Imperial)**

2.0

**Bundle Diameter Max (Metric)**

50.0

**Thickness T (Imperial)**

0.05

<b>Thickness T (Metric)</b>	1.2
<b>Height H (Imperial)</b>	0.61
<b>Height H (Metric)</b>	15.5
<b>Panel Thickness Min(Imperial)</b>	0.04
<b>Panel Thickness Max(Imperial)</b>	0.12
<b>Panel Thickness Min (Metric)</b>	1.0
<b>Panel Thickness Max (Metric)</b>	3.0
<b>Material</b>	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV) Polyamide 6.6, high impact modified, heat and UV-stabilized, proprietary blend (PA66HIRHSUVR5)
<b>Material Shortcut</b>	PA66HIRHSUV PA66HIRHSUVR5
<b>Material Cable Tie</b>	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
<b>Flammability</b>	UL 94 HB
<b>Operating Temperature (Metric)</b>	-40°F to +230°F (-40°C to +110°C) -40°F to +239°F (-40°C to +115°C)
<b>ROHS Complaint</b>	Yes
<b>Package Quantity(Imperial)</b>	100

**Package Quantity (Metric)** 100

**Customs Number** 3926909988

**Weight (Metric)** 0.00281227

**Weight (Imperial)** 0.0062