

Specification Sheet

Part Number: 156-02259



MOC Clip, 22 mm Transverse, Assembled to T50SVC Swivel Tie, PA66HIRHSUV, Black, 1000/ctn

Article Number

156-02259

Type

T50SVCMOC22M180

Color

Black (BK)

Features & Benefits

- Patented retention design on clip features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement.
- Controlled flex and angled entry promote easy installation.
- Independent rotation allows for adjustable routing orientation.
- Cable tie accommodates wide range of secondary bundle sizes.

Quantity Per

carton

Product Description

The MOC 180 to Swivel Tie is a rotatable routing clip coupled to a cable tie that keeps two routings secured and separated. Tie provides additional security against axial slip by clamping around solid tube, pipe or harness. The clip's orientation allows the second routing to be assembled in the direction of the first routing. The swivel coupler allows the two routings to rotate independently of each other.

Short Description

MOC Clip, 22 mm Transverse, Assembled to T50SVC Swivel Tie, PA66HIRHSUV, Black, 1000/ctn

Global Part Name

T50SVCMOC22M180-PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial)

50

Minimum Tensile Strength (Metric)

225

Length L (Imperial)

1.20

Length L (Metric)

30.5

Fixation Method

Omega Clips

Identification Plate Position

none

Bundle Diameter Min (Imperial)

0.79

Bundle Diameter Min (Metric)

20.0

Bundle Diameter Max (Imperial)

0.98

Bundle Diameter Max (Metric)

25.0

Height H (Imperial)

1.88

Height H (Metric)

47.8

Depth D (imperial)

0.47

Depth D (metric)

12.0

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen free	Yes
Operating Temperature (Metric)	-40°F to +230°F (-40°C to +110°C)
ROHS Complaint	Yes
Package Quantity(Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988
Weight (Metric)	3.76
Weight (Imperial)	0.13