

Specification Sheet

Part Number: 156-02266



Bi-directional saddle allows for the securing of bundles perpendicular or parallel to mounting hole.

HellermannTyton's 4x oval prevents bundle rotation while providing best-in-class installation and extraction resistance for four common oval sizes.

2-Piece Cable Tie/Fir Tree Mount, Unassembled Set, 110mm Max Bundle, PA66HIRHSUV, Black, 3000/ctn

Article Number 156-02266

Type T50LSADFTOVAL-SET

Color Black (BK)

Quantity Per carton

Product Description These two-piece fasteners offer a simple and versatile method of bundling and mounting cables up to 4.3" (110 mm) to a panel up to 6.0 mm thick using an oval hole. The fir tree will easily push into pre-punched holes in panels or threaded blind holes and offers a secure fit. The two-piece design enables the head of the tie to be oriented in the required position to ease assembly, while the disc on top of the fir tree covers the hole and minimizes the ingress of water and dirt.

Short Description 2-Piece Cable Tie/Fir Tree Mount, Unassembled Set, 110mm Max Bundle, PA66HIRHSUV, Black, 3000/ctn

Global Part Name T50LSADFTOVAL-SET-PA66HS/PA66HIRHS-BK

Minimum Tensile Strength (Imperial) 50.0

Minimum Tensile Strength (Metric) 225

Length L (Imperial) 15.0

Length L (Metric) 381.0

Fixation Method Fir Tree for oval holes

Identification Plate Position none

Tie Closure plastic pawl

Width W (Imperial) 0.694

Width W (Metric) 17.63

Bundle Diameter Min (Imperial) 0.197

Bundle Diameter Min (Metric) 5.0

Bundle Diameter Max (Imperial) 4.33

Bundle Diameter Max (Metric) 110.0

Height H (Imperial) 0.787

Height H (Metric) 20

Mounting Hole Diameter D (Imperial)	0.24 " X 0.48 " 0.26 " X 0.49 " 0.25 " X 0.51" 0.28 " X 0.47
Mounting Hole Diameter D (Metric)	6.5 x 13.0 mm 6.2 x 12.2 mm 6.5 x 12.5 mm 7.0 x 12.0 mm
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS) Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HIRHS PA66HS
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
ROHS Compliant	Yes
Package Quantity (Imperial)	3000
Package Quantity (Metric)	3000
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).