

## Specification Sheet

Part Number: 156-02284



MOC Clip to MOC Clip, 5 mm, 9 mm, PA66HIRHSUV, Black, 1000/ctn

**Article Number**

156-02284

**Type**

MOC5FMOC9M

**Color**

Black (BK)

**Features & Benefits**

- Patented retention design features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement.
- Controlled flex and angled entry promote easy installation.
- Independent rotation allows for adjustable routing orientation.

**Quantity Per**

carton

**Product Description**

The MOC to MOC is a rotatable dual routing clip that keeps two routings secured and separated. A swivel coupler allows them to rotate independently of each other.

**Short Description**

MOC Clip to MOC Clip, 5 mm, 9 mm, PA66HIRHSUV, Black, 1000/ctn

**Global Part Name**

MOC5FMOC9M-PA66HIRHSUV-BK

**Length L (Imperial)**

1.17

**Length L (Metric)**

29.7

**Variant**

Clip to Clip

**Bundle Diameter Min (Imperial)**

0.16

**Bundle Diameter Min (Metric)**

4.0

**Bundle Diameter Max (Imperial)**

0.22

**Bundle Diameter Max (Metric)**

5.5

**Height H (Imperial)**

0.68

**Height H (Metric)**

17.2

**Depth D (imperial)**

0.39

**Depth D (metric)**

10.0

**Material**

Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

**Material Shortcut**

PA66HIRHSUV

**Flammability**

UL 94 HB

**Halogen free** Yes

**Operating Temperature (Metric)** -40°F to +230°F (-40°C to +110°C)

**ROHS Complaint** Yes

**Package Quantity(Imperial)** 1000

**Package Quantity (Metric)** 1000

**Customs Number** 3926909988

**Weight (Metric)** 1.42

**Weight (Imperial)** 0.05