

## Specification Sheet

Part Number: 156-02289



MOC Clip to MOC Clip, 5 mm, 19 mm, PA66HIRHSUV, Black, 1000/ctn

<b>Article Number</b>	156-02289
<b>Type</b>	MOC5FMOC19M
<b>Color</b>	Black (BK)
<b>Features &amp; Benefits</b>	<ul style="list-style-type: none"><li>• Patented retention design features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement.</li><li>• Controlled flex and angled entry promote easy installation.</li><li>• Independent rotation allows for adjustable routing orientation.</li></ul>
<b>Quantity Per</b>	carton
<b>Product Description</b>	The MOC to MOC is a rotatable dual routing clip that keeps two routings secured and separated. A swivel coupler allows them to rotate independently of each other.
<b>Short Description</b>	MOC Clip to MOC Clip, 5 mm, 19 mm, PA66HIRHSUV, Black, 1000/ctn

**Global Part Name**

MOC5FMOC19M-PA66HIRHSUV-BK

**Length L (Imperial)**

1.65

**Length L (Metric)**

42.0

**Variant**

Clip to Clip

**Bundle Diameter Min (Imperial)**

0.16

**Bundle Diameter Min (Metric)**

4.0

**Bundle Diameter Max (Imperial)**

0.22

**Bundle Diameter Max (Metric)**

5.5

**Height H (Imperial)**

1.29

**Height H (Metric)**

32.8

**Depth D (imperial)**

0.47

**Depth D (metric)**

12.0

**Material**

Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

**Material Shortcut**

PA66HIRHSUV

**Flammability**

UL 94 HB

**Halogen free** Yes

**Operating Temperature (Metric)** -40°F to +230°F (-40°C to +110°C)

**ROHS Complaint** Yes

**Package Quantity(Imperial)** 1000

**Package Quantity (Metric)** 1000

**Customs Number** 3926909988

**Weight (Metric)** 3.5

**Weight (Imperial)** 0.12