

## Specification Sheet

Part Number: 156-02296



**Article Number**

156-02296

**Type**

MOC6FMOC9M

**Color**

Black (BK)

**Features & Benefits**

- Patented retention design features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement.
- Controlled flex and angled entry promote easy installation.
- Independent rotation allows for adjustable routing orientation.

**Quantity Per**

carton

**Product Description**

The MOC to MOC is a rotatable dual routing clip that keeps two routings secured and separated. A swivel coupler allows them to rotate independently of each other.

**Short Description**

MOC Clip to MOC Clip, 6 mm, 9 mm, PA66HIRHSUV, Black, 1000/ctn

Global Part Name

MOC6FMOC9M-PA66HIRHSUV-BK

Length L (Imperial)

1.22

Length L (Metric)

31.0

Variant

Clip to Clip

Bundle Diameter Min (Imperial)

0.22

Bundle Diameter Min (Metric)

5.5

Bundle Diameter Max (Imperial)

0.27

Bundle Diameter Max (Metric)

6.8

Height H (Imperial)

0.68

Height H (Metric)

17.2

Depth D (imperial)

0.39

Depth D (metric)

10.0

Material

Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

Material Shortcut

PA66HIRHSUV

Flammability

UL 94 HB

**Halogen free** Yes

**Operating Temperature (Metric)** -40°F to +230°F (-40°C to +110°C)

**ROHS Complaint** Yes

**Package Quantity(Imperial)** 1000

**Package Quantity (Metric)** 1000

**Customs Number** 3926909988

**Weight (Metric)** 1.49

**Weight (Imperial)** 0.05