

## Specification Sheet

Part Number: 156-02305



**Article Number**

156-02305

**Type**

MOC7FMOC7M

**Color**

Black (BK)

**Features & Benefits**

- Patented retention design features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement.
- Controlled flex and angled entry promote easy installation.
- Independent rotation allows for adjustable routing orientation.

**Quantity Per**

carton

**Product Description**

The MOC to MOC is a rotatable dual routing clip that keeps two routings secured and separated. A swivel coupler allows them to rotate independently of each other.

**Short Description**

MOC Clip to MOC Clip, 7 mm, 7 mm, PA66HIRHSUV, Black, 2000/ctn

**Global Part Name**

MOC7FMOC7M-PA66HIRHSUV-BK

**Length L (Imperial)**

1.13

**Length L (Metric)**

28.6

**Variant**

Clip to Clip

**Bundle Diameter Min (Imperial)**

0.24

**Bundle Diameter Min (Metric)**

6.0

**Bundle Diameter Max (Imperial)**

0.31

**Bundle Diameter Max (Metric)**

8.0

**Height H (Imperial)**

0.53

**Height H (Metric)**

13.4

**Depth D (imperial)**

0.39

**Depth D (metric)**

10.0

**Material**

Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

**Material Shortcut**

PA66HIRHSUV

**Flammability**

UL 94 HB

**Halogen free** Yes

**Operating Temperature (Metric)** -40°F to +230°F (-40°C to +110°C)

**ROHS Complaint** Yes

**Package Quantity(Imperial)** 2000

**Package Quantity (Metric)** 2000

**Customs Number** 3926909988

**Weight (Metric)** 1.21

**Weight (Imperial)** 0.04