

Specification Sheet

Part Number: 156-02317



Article Number

156-02317

Type

MOC8FMOC9M

Color

Black (BK)

Features & Benefits

- Patented retention design features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement.
- Controlled flex and angled entry promote easy installation.
- Independent rotation allows for adjustable routing orientation.

Quantity Per

carton

Product Description

The MOC to MOC is a rotatable dual routing clip that keeps two routings secured and separated. A swivel coupler allows them to rotate independently of each other.

Short Description

MOC Clip to MOC Clip, 8 mm, 9 mm, PA66HIRHSUV, Black, 1000/ctn

Global Part Name

MOC8FMOC9M-PA66HIRHSUV-BK

Length L (Imperial)

1.31

Length L (Metric)

33.3

Variant

Clip to Clip

Bundle Diameter Min (Imperial)

0.28

Bundle Diameter Min (Metric)

7.0

Bundle Diameter Max (Imperial)

0.35

Bundle Diameter Max (Metric)

9.0

Height H (Imperial)

0.68

Height H (Metric)

17.2

Depth D (imperial)

0.39

Depth D (metric)

10.0

Material

Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

Material Shortcut

PA66HIRHSUV

Flammability

UL 94 HB

Halogen free Yes

Operating Temperature (Metric) -40°F to +230°F (-40°C to +110°C)

ROHS Complaint Yes

Package Quantity(Imperial) 1000

Package Quantity (Metric) 1000

Customs Number 3926909988

Weight (Metric) 1.69

Weight (Imperial) 0.06