

Specification Sheet

Part Number: 156-02435



2-Piece Cable Tie/Fir Tree Mount, 8mm Hole and M10 Threaded Hole, PA46, Brown, 1200/ctn

Article Number

156-02435

Type

WSSDFTM10WSSDSET

Color

Brown (BN)

Features & Benefits

- Versatile and robust fir tree design provides low insertion effort yet delivers exceptional retention strength in an 6.5 mm hole and M8 threaded hole.
- Wider and thinner strap design increases flexibility and minimizes pinching of bundles, hoses and tubing.
- PA46 nylon material provides great performance at up to 135°F continuous operating temperature.

Quantity Per

carton

Product Description

These two-piece fasteners are pre-assembled and offer a simple and versatile method of bundling and mounting cables. Sold as an unassembled set, this oval fir tree and tie combination allows the user to install the tie in two different directions, securing the bundle perpendicular or inline to the oval mounting hole.

Short Description

2-Piece Cable Tie/Fir Tree Mount, 8mm Hole and M10 Threaded Hole, PA46, Brown, 1200/ctn

Global Part Name

WSSDFTM10WSSDSET-PA46-BN

Minimum Tensile Strength (Imperial)

120.0

Minimum Tensile Strength (Metric)

533.0

Length L (Imperial)

9.1

Length L (Metric)

231.14

Fixation Method

Fir Tree

Identification Plate Position

none

Releasable Closure

No

Tie Closure

plastic pawl

Variant

Inside Serrated

Width W (Imperial)

0.88

Width W (Metric)

22.6

Bundle Diameter Max (Imperial)

2.25

Bundle Diameter Max (Metric)

57.15

Height H (Imperial)

0.98

Height H (Metric)	23.7
--------------------------	------

Mounting Hole Diameter D (Imperial) 0.314

Mounting Hole Diameter D (Metric)	8.0 mm
--	--------

Material	Polyamide 4.6 (PA46)
-----------------	----------------------

Material Shortcut PA46

Operating Temperature (Metric)	-40°F to +266°F (-40°C to +130°C)
---------------------------------------	-----------------------------------

Reach Complaint(Article 33) Yes

ROHS Complaint	Yes
-----------------------	-----

Package Quantity(Imperial)	1200
-----------------------------------	------

Package Quantity (Metric) 1200

Customs Number	3926909988
-----------------------	------------

Content Unit(BMEcat) pcs.

