

Specification Sheet

Part Number: 156-02513



Article Number

156-02513

Type

T50RPBM9SET

Color

Black (BK)

Features & Benefits

- Capable of holding several cables, depending on cable tie size, for ultimate flexibility.
- Zero-insertion-force design requires no tools for quick and easy mounting.
- High impact modified, heat-resistant, UV stabilized material is ideal for long-term performance, even in extreme weather.

Quantity Per

bag

Product Description

This button head mount includes a cable tie to secure cables and wire bundles to panels. Once placed through the panel hole, installers can insert the cable tie through the mount on the panel's opposite surface. The button head mount is designed to fit pre-stamped oval hole sizes from 9x12 mm to 9x14 mm with zero insertion force. Made from impact-modified, heat-resistant, UV stabilized Polyamide 6.6 material, it will withstand extreme environments.

Short Description	Cable Tie with Button Mount, 0.35" Hole Dia, 0.12" Max Panel, 0.07" Max Tie Width, PA66HIRHSUV, Blk, 1000/pkg
Global Part Name	T50RPBM9SET-PA66HIRHSUV-BK
Minimum Tensile Strength (Imperial)	50.0
Minimum Tensile Strength (Metric)	225.0
Length L (Imperial)	8.0
Length L (Metric)	203.2
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Width W (Imperial)	0.67
Width W (Metric)	17.0
Bundle Diameter Max (Imperial)	1.97
Bundle Diameter Max (Metric)	50.0
Cable Ties	T50R
Height H (Imperial)	0.53
Height H (Metric)	13.40

Panel Thickness Max(Imperial)

0.12

Panel Thickness Max (Metric)

3.0

Mounting Hole Diameter D (Imperial)

0.35 x 0.47 ", 0.35 x 0.55

Mounting Hole Diameter D (Metric)

9.0 x 14.0 mm 9.0 x 12.0 mm

Material

Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

Material Shortcut

PA66HIRHSUV

Flammability

UL 94 HB

Operating Temperature (Metric)

-40°F to +230°F (-40°C to +110°C)

ROHS Complaint

Yes

UL Recognized (US)

Yes

UL Listed (US and Canada)

Yes

UL Recognized (US and Canada)

Yes

Package Quantity(Imperial)

1000

Package Quantity (Metric)

1000

Customs Number

3926909988

© 2019 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)