

## Specification Sheet

Part Number: 156-02916

Multi option stud mount clip secures bundles running alongside a bolt or stud.

Patented retention design features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement.

Controlled flex and angled entry promote easy installation.

Independent rotation allows for adjustable routing orientation.

High-performance stud mount design allows for easy installation and delivers outstanding stud retention to keep bundles secure.



Stud Mount to MOC Clip, 22mm Clip, 5mm/6mm Stud Mount, PA66HIRHSUV, Black, 1000/ctn

Article Number 156-02916

Type SMF2MOC22M

Color Black (BK)

Quantity Per carton

Product Description The MOC with stud mount features HellermannTyton's unique retention clip with a best-in-class stud mount to secure to a 5mm or 6mm stud or bolt. The mount delivers a low insertion force while exhibiting high extraction resistance for a secure mounting point.

Short Description	Stud Mount to MOC Clip, 22mm Clip, 5mm/6mm Stud Mount, PA66HIRHSUV, Black, 1000/ctn
Global Part Name	SMF2MOC22M-PA66HIRHSUV-BK
Length L (Imperial)	2.23
Length L (Metric)	56.6
Fixation Method	Stud Mount
Bundle Diameter Min (Imperial)	0.79
Bundle Diameter Min (Metric)	20.0
Bundle Diameter Max (Imperial)	0.98
Bundle Diameter Max (Metric)	25.0
Height H (Imperial)	1.54
Height H (Metric)	39.2
Depth D (Imperial)	0.61
Depth D (Metric)	15.5
Mounting Hole Diameter D (Metric)	6.0 mm 5.0 mm
Stud Diameter (Metric)	6.0 mm 5.0 mm
Stud Diameter (Imperial)	0.20 ";0.24

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +230°F (-40°C to +110°C)
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988