

Specification Sheet

Part Number: 156-02933

Multi option stud mount clamp secures bundles above a bolt or stud.

The 360 degree locking enclosure and cable tie dynamically fit a range of bundle sizes.

Clamp can be opened for bundle maintenance.

Independent rotation allows for adjustable routing orientation.

High-performance stud mount design allows for easy installation and delivers outstanding stud retention to keep bundles secure.



Stud Mount to LOC Locking Clamp, 20-25mm Clamp, 5mm/6mm Stud Mount, PA66HIRHSUV, Black, 1000/ctn

Article Number 156-02933

Type SMF2LOC20-25

Color Black (BK)

Quantity Per carton

Product Description The LOC with stud mount features HellermannTyton's locking option clamp with a best-in-class stud mount to secure to a 5mm or 6mm stud or bolt. The mount delivers a low insertion force while exhibiting high extraction resistance for a secure mounting point.

Short Description	Stud Mount to LOC Locking Clamp, 20-25mm Clamp, 5mm/6mm Stud Mount, PA66HIRHSUV, Black, 1000/ctn
Global Part Name	SMF2LOC20-25-PA66HIRHSUV-BK
Length L (Imperial)	2.40
Length L (Metric)	61.0
Fixation Method	Stud Mount
Bundle Diameter Min (Imperial)	0.79
Bundle Diameter Min (Metric)	20.0
Bundle Diameter Max (Imperial)	0.98
Bundle Diameter Max (Metric)	25.0
Height H (Imperial)	1.56
Height H (Metric)	39.7
Depth D (Imperial)	0.61
Depth D (Metric)	15.5
Nominal Diameter (Metric)	22.5
Mounting Hole Diameter D (Metric)	5.0 mm 6.0 mm
Stud Diameter (Metric)	M5 M6 T5 T6

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +230°F (-40°C to +110°C)
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988