

## Specification Sheet

Part Number: 156-04601



Outside Serrated Cable Tie & Edge Clip, 6.0" Long, EC19, 3-6 mm Panel, 50lb, PA66HS, Black, 500/pkg

Article Number	156-04601
Type	T50SOSEC19
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none"><li>•Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole.</li><li>•Edge Clip provides low insertion force and high extraction force ideal for assembly environments.</li><li>•Two piece assembly allows the mount to slide along the strap ensuring proper orientation.</li><li>•Cable tie is outside serrated to reduce bundle chafing.</li></ul>
Quantity Per	bag

### Product Description

HellermannTyton's Two Piece Edge Clip with Cable Tie Assemblies are designed specifically to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. The clip is easy to secure and the extraction force is high due to the integrated metal clamp that holds the edge clip in place.

**Short Description**

Outside Serrated Cable Tie &amp; Edge Clip, 6.0" Long, EC19, 3-6 mm Panel, 50lb, PA66HS, Black, 500/pkg

**Global Part Name**

T50SOSEC19-PA66HS/PA66HIRHS-BK

**Minimum Tensile Strength (Imperial)**

50.0

**Minimum Tensile Strength (Metric)**

225

**Length L (Imperial)**

6.0

**Length L (Metric)**

150.0

**Fixation Method**

EdgeClip, top, assembled, 2 piece

**Identification Plate Position**

none

**Variant**

Outside Serrated

**Width W (Imperial)**

0.18

**Width W (Metric)**

4.6

**Bundle Diameter Min (Imperial)**

0.20

**Bundle Diameter Min (Metric)**

1.0

**Bundle Diameter Max (Imperial)**

1.4

**Bundle Diameter Max (Metric)**

35.0

**Thickness T (Imperial)**

0.05

<b>Height H (Imperial)</b>	0.05
<b>Height H (Metric)</b>	1.3
<b>Panel Thickness Min(Imperial)</b>	0.12
<b>Panel Thickness Max(Imperial)</b>	0.24
<b>Panel Thickness Min (Metric)</b>	3.0
<b>Panel Thickness Max (Metric)</b>	6.0
<b>Material</b>	Polyamide 6.6 heat stabilized (PA66HS) Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
<b>Material Shortcut</b>	PA66HS PA66HIRHS
<b>Material Cable Tie</b>	Polyamide 6.6 heat stabilized (PA66HS)
<b>Flammability</b>	UL 94 HB
<b>Operating Temperature (Metric)</b>	-40°F to +221°F (-40°C to +105°C)
<b>Reach Complaint(Article 33)</b>	Yes
<b>ROHS Complaint</b>	Yes
<b>Package Quantity(Imperial)</b>	500
<b>Package Quantity (Metric)</b>	500

**Customs Number**

3926909988

**Content Unit(BMEcat)**

pcs.

**Weight (Metric)**

1.9