

Specification Sheet

Part Number: 157-00036



Article Number

157-00036

Type

WSR8MM

Color

Black (BK)

Features & Benefits

- Mount provides low insertion and high extraction forces which makes for a strong and easy installation.
- Tie utilizes a strong hinge between the stud mount and strap head to provide superior holding ability.
- Clamping rails increase grip on round bundles.
- Thinner strap provides increased flexibility for improved ergonomics.

Quantity Per

bag

Product Description

The Wide Strap Stud Mount Cable Tie minimizes pinching on soft bundles and features a low profile head to provide compact bundling. A thinner strap provides increased flexibility for improved ergonomics. Available in various stud mount sizes, the wide strap tie utilizes a strong hinge between the stud mount and head to provide superior holding ability on a threaded stud.

Short Description	Wide Strap Cable Tie with 8mm Stud Mount, 15.7" Long, .5" Wide, PA66HIRHSUV, Black, 300/Bag
Global Part Name	WSR8MM-PA66HIRHSUV-BK
Minimum Tensile Strength (Imperial)	120
Minimum Tensile Strength (Metric)	534
Length L (Imperial)	15.7
Length L (Metric)	398.8
Fixation Method	Weld Stud Fixing
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.5
Width W (Metric)	12.7
Bundle Diameter Min (Imperial)	0.38
Bundle Diameter Min (Metric)	9.5
Bundle Diameter Max (Imperial)	4.1

Bundle Diameter Max (Metric)

104.1

Stud Diameter (Metric)

M8

Stud Diameter (Imperial)

5/16

Material

Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

Material Shortcut

PA66HIRHSUV

Flammability

UL 94 HB

Operating Temperature (Metric)

-40°F to +230°F (-40°C to +110°C)

Reach Complaint(Article 33)

Yes

ROHS Complaint

Yes

Package Quantity(Imperial)

300

Package Quantity (Metric)

300

Customs Number

3926909988

Content Unit(BMEcat)

pcs.

