

Specification Sheet

Part Number: 157-00052



Article Number	157-00052
Type	T50ROSFT6LGU
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">•All-in-one bundling and fastening solution reduces costs and assembly time.•Disc feature provides anti-rattle protection in high-vibration applications.
Quantity Per	bag
Product Description	One-piece mounting ties offer a complete solution by both bundling and mounting wires, cables and tubes. The fir tree mount provides low insertion force with a high extraction force. Outside serrations on the cable tie leave a smooth interior surface that's gentler on sensitive wire insulation. The unique head design allows the cable tie to firmly hold bundles as small as .06" diameter. The disc offers added protection against debris.
Short Description	1-Piece Cable Tie/Fir Tree Mount with Disc, 8.5"L, 6.5–7.2 mm Mounting Hole, PA66HS, Black, 500/pkg

Global Part Name

T50ROSFT6LGU-PA66HS-BK

Minimum Tensile Strength (Imperial)

50.0

Minimum Tensile Strength (Metric)

225

Length L (Imperial)

8.6

Length L (Metric)

218.44

Fixation Method

Fir Tree

Identification Plate Position

none

Releasable Closure

No

Tie Closure

plastic pawl

Variant

Outside Serrated

Width W (Imperial)

0.2

Width W (Metric)

5.1

Bundle Diameter Max (Imperial)

2.0

Bundle Diameter Max (Metric)

50.0

Thickness T (Imperial)

0.06

Thickness T (Metric)

1.5

Height H (Imperial)

0.06

Height H (Metric)	1.5
Panel Thickness Min(Imperial)	0.02
Panel Thickness Max(Imperial)	0.33
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	8.5
Mounting Hole Diameter D (Imperial)	0.283 - 0.255
Mounting Hole Diameter D (Metric)	6.5 - 7.2 mm
Mounting Hole Diameter D Min (Imperial)	0.255
Mounting Hole Diameter D Max (Imperial)	0.283
Mounting Hole Diameter D Max (Metric)	7.2
Disc Diameter(Metric)	15.9
Disc Diameter (Imperial)	0.63
Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL 94 V2
Operating Temperature (Metric)	-40°F to +221°F (-40°C to +105°C)

Reach Complaint(Article 33)

Yes

ROHS Complaint

Yes

Package Quantity(Imperial)

500

Package Quantity (Metric)

500

Customs Number

3926909988

Content Unit(BMEcat)

pcs.