

Specification Sheet

Part Number: 157-00068



Article Number

157-00068

Type

OS180FT7LH

Color

Gray (GY)

Features & Benefits

- Friction tab inside of fir tree allows tie to sit in mount without falling out prior to installation.
- Initial fir tree serves as a locating feature for assistance in blind assembly applications.
- Disc feature provides anti-rattle protection in high vibration applications.

Quantity Per

bag

Product Description

Fir tree mounts with ties cables provide a secure grip in mounting holes and protect against dirt and other impurities. The mount provides low insertion and high extraction force, and slides along the cable tie for the proper orientation. This is sold as an assembly with the cable tie.

Short Description

1-Piece Cable Tie/Fir Tree Mount, 6.7" Long, Mounting Hole Diameter 0.24" - 0.26", PA66, Grey, 500/pkg

Global Part Name

OS180FT7LH-PA66-GY

Minimum Tensile Strength (Imperial)

50.0

Minimum Tensile Strength (Metric)

200

Length L (Imperial)

7.0

Length L (Metric)

180.0

Fixation Method

Flat profile

Identification Plate Position

none

Releasable Closure

No

Tie Closure

plastic pawl

Width W (Imperial)

0.21

Width W (Metric)

5.3

Bundle Diameter Min (Imperial)

0.06

Bundle Diameter Min (Metric)

1.6

Bundle Diameter Max (Imperial)

1.18

Bundle Diameter Max (Metric)

30.0

Thickness T (Metric)

1.4

Height H (Imperial)

0.7

Panel Thickness Min(Imperial)	0.03
Panel Thickness Max(Imperial)	0.18
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	4.5
Mounting Hole Diameter D (Imperial)	0.24 - 0.26
Mounting Hole Diameter D (Metric)	6.5 - 7.0 mm 6.35 mm (hexagonal)
Mounting Hole Diameter D Max (Metric)	7.0
Disc Diameter(Metric)	16.0
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Package Quantity(Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

