

## Specification Sheet

Part Number: 157-00105



<b>Article Number</b>	157-00105
<b>Type</b>	T50SOSSB5-High-E-C-CC
<b>Color</b>	Black (BK)
<b>Features &amp; Benefits</b>	<ul style="list-style-type: none"><li>• Head allows for a .2" lateral adjustment on stud during installation.</li><li>• Quick and easy installation ideal for manufacturing environment.</li></ul>
<b>Quantity Per</b>	bag
<b>Product Description</b>	Oval Shaped Stud Mount's special design allows for a .20" (5.5 mm) lateral adjustment, allowing for any misalignment of the stud or incorrect position of the tie on the cables. The mount allows it to be installed onto a weld stud without the use of any tools.
<b>Short Description</b>	1-Piece Cable Tie/Oval Stud Mount, 6.6" Long, 50lb Tensile, With Thumb Bar, PA66HS, Black, 3000/pkg

Global Part Name

T50SOSSB5-High-E-C-CC-PA66HS-BK

Minimum Tensile Strength (Imperial)

50.0

Minimum Tensile Strength (Metric)

225

Length L (Imperial)

6.6

Length L (Metric)

167.0

Fixation Method

Weld Stud Fixing

Identification Plate Position

none

Releasable Closure

No

Tie Closure

plastic pawl

Variant

Outside Serrated

Width W (Imperial)

0.2

Width W (Metric)

5.0

Bundle Diameter Min (Imperial)

0.04

Bundle Diameter Min (Metric)

1.0

Bundle Diameter Max (Imperial)

1.4

Bundle Diameter Max (Metric)

35.0

Stud Length Max (Imperial)

0.56

<b>Stud Length Max (Metric)</b>	14.2
---------------------------------	------

**Stud Diameter (Metric)** 5.0 mm

<b>Stud Diameter (Imperial)</b>	0.20
---------------------------------	------

<b>Material</b>	Polyamide 6.6 heat stabilized (PA66HS)
-----------------	--

**Material Shortcut** PA66HS

<b>Flammability</b>	UL 94 V2
---------------------	----------

**Operating Temperature (Metric)** -40°F to +221°F (-40°C to +105°C)

<b>ROHS Complaint</b>	Yes
-----------------------	-----

<b>Package Quantity(Imperial)</b>	3000
-----------------------------------	------

**Package Quantity (Metric)** 3000

<b>Customs Number</b>	3926909988
-----------------------	------------

**Content Unit(BMEcat)** bag

