

## Specification Sheet

Part Number: 157-00282



**Article Number**

157-00282

**Type**

WSI6MM

**Color**

Black (BK)

**Features & Benefits**

- Mount provides low insertion and high extraction forces which makes for a strong and easy installation.
- Tie utilizes a strong hinge between the stud mount and strap head to provide superior holding ability.
- Clamping rails increase grip on round bundles.
- Thinner strap provides increased flexibility for improved ergonomics.

**Quantity Per**

bag

**Product Description**

The Wide Strap Stud Mount Cable Tie minimizes pinching on soft bundles and features a low profile head to provide compact bundling. A thinner strap provides increased flexibility for improved ergonomics. Available in various stud mount sizes, the wide strap tie utilizes a strong hinge between the stud mount and head to provide superior holding ability on a threaded stud.

<b>Short Description</b>	Wide Strap Cable Tie with 6mm Stud Mount, 12.7" Long, .5" Wide, PA66HIRHSUV, Black, 300/Bag
<b>Global Part Name</b>	WSI6MM-PA66HIRHSUV-BK
<b>Minimum Tensile Strength (Imperial)</b>	120
<b>Minimum Tensile Strength (Metric)</b>	534
<b>Length L (Imperial)</b>	12.7
<b>Length L (Metric)</b>	322.6
<b>Fixation Method</b>	Weld Stud Fixing
<b>Identification Plate Position</b>	none
<b>Releasable Closure</b>	No
<b>Tie Closure</b>	plastic pawl
<b>Variant</b>	Inside Serrated
<b>Width W (Imperial)</b>	0.5
<b>Width W (Metric)</b>	12.7
<b>Bundle Diameter Min (Imperial)</b>	0.38
<b>Bundle Diameter Min (Metric)</b>	9.5
<b>Bundle Diameter Max (Imperial)</b>	3.2

<b>Bundle Diameter Max (Metric)</b>	82.5
<b>Stud Diameter (Metric)</b>	M6
<b>Stud Diameter (Imperial)</b>	1/4
<b>Material</b>	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
<b>Material Shortcut</b>	PA66HIRHSUV
<b>Flammability</b>	UL 94 HB
<b>Operating Temperature (Metric)</b>	-40°F to +230°F (-40°C to +110°C)
<b>ROHS Complaint</b>	Yes
<b>Package Quantity(Imperial)</b>	300
<b>Package Quantity (Metric)</b>	300
<b>Customs Number</b>	3926909988
<b>Content Unit(BMEcat)</b>	bag

