

Specification Sheet

Part Number: 157-00340



Article Number

157-00340

Type

T80ROSLPSB8U

Color

Black (BK)

Features & Benefits

- Low-profile head allows mounts to stack, providing more mounting versatility from a single stud.
- Four-pawl, three-tooth design delivers outstanding stud retention to keep bundles secure.
- PA46 material option allows use in high-heat applications.

Quantity Per

carton

Product Description

Mount features a low-profile head, allowing multiple tie mounts to be stacked on a single bolt and providing space savings in tight areas. With their low insertion force and high extraction performance, HellermannTyton mounting ties offer the ideal combination of high-grade materials and superior design to suit the mounting and bundling needs of complex applications. Available in standard and high-heat material options.

Short Description

Low-Profile M8 Stud Mount Tie, 7.5" Tie, 80lb Tensile Strength, PA66HIRHS, Black, 3000/pkg

Global Part Name

T80ROSLPSB8U-PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial)

80.0

Minimum Tensile Strength (Metric)

355

Length L (Imperial)

8.3

Length L (Metric)

212.0

Fixation Method

Stud Mount

Identification Plate Position

none

Releasable Closure

No

Tie Closure

plastic pawl

Width W (Imperial)

0.70

Width W (Metric)

17.75

Bundle Diameter Min (Imperial)

0.14

Bundle Diameter Min (Metric)

3.5

Bundle Diameter Max (Imperial)

1.97

Bundle Diameter Max (Metric)

50.0

Cable Ties	157-00340
Height H (Imperial)	0.25
Height H (Metric)	6.30
Mounting Hole Diameter D (Imperial)	0.31" x 0.05
Mounting Hole Diameter D (Metric)	M8 x 1.25
Stud Diameter (Metric)	8.0 mm
Stud Diameter (Imperial)	0.31
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Operating Temperature (Metric)	-40°F to +230°F (-40°C to +110°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Package Quantity(Imperial)	3000
Package Quantity (Metric)	3000

Customs Number

3926909988

Content Unit(BMEcat)

pcs.

Weight (Metric)

0.0026

Weight (Imperial)

0.006