

## Specification Sheet

Part Number: 157-00343



**Article Number**

157-00343

**Type**

T80ROSLPSB10U

**Color**

Brown (BN)

**Features & Benefits**

- Low-profile head allows mounts to stack, providing more mounting versatility from a single stud.
- Four-pawl, three-tooth design delivers outstanding stud retention to keep bundles secure.
- PA46 material option allows use in high-heat applications.

**Quantity Per**

carton

**Product Description**

Mount features a low-profile head, allowing multiple tie mounts to be stacked on a single bolt and providing space savings in tight areas. With their low insertion force and high extraction performance, HellermannTyton mounting ties offer the ideal combination of high-grade materials and superior design to suit the mounting and bundling needs of complex applications. Available in standard and high-heat material options.

<b>Short Description</b>	Low-Profile M10 Stud Mount Tie, 7.5" Tie, 80lb Tensile Strength, PA46, Brown, 3500/pkg
<b>Global Part Name</b>	T80ROSLPSB10U-PA46-BN
<b>Minimum Tensile Strength (Imperial)</b>	80.0
<b>Minimum Tensile Strength (Metric)</b>	355
<b>Length L (Imperial)</b>	8.5
<b>Length L (Metric)</b>	215.9
<b>Fixation Method</b>	Stud Mount
<b>Identification Plate Position</b>	none
<b>Releasable Closure</b>	No
<b>Tie Closure</b>	plastic pawl
<b>Width W (Imperial)</b>	0.22
<b>Width W (Metric)</b>	10.0
<b>Bundle Diameter Min (Imperial)</b>	0.14
<b>Bundle Diameter Min (Metric)</b>	3.5
<b>Bundle Diameter Max (Imperial)</b>	1.97
<b>Bundle Diameter Max (Metric)</b>	50.0

<b>Cable Ties</b>	157-00343
<b>Height H (Imperial)</b>	0.28
<b>Height H (Metric)</b>	7.0
<b>Mounting Hole Diameter D (Imperial)</b>	0.39" x 0.06
<b>Mounting Hole Diameter D (Metric)</b>	M10 x 1.50
<b>Stud Diameter (Metric)</b>	10.0 mm
<b>Stud Diameter (Imperial)</b>	0.39
<b>Material</b>	Polyamide 4.6 (PA46)
<b>Material Shortcut</b>	PA46
<b>Operating Temperature (Metric)</b>	-40°F to +266°F (-40°C to +130°C)
<b>Reach Complaint(Article 33)</b>	Yes
<b>ROHS Complaint</b>	Yes
<b>Package Quantity(Imperial)</b>	3500
<b>Package Quantity (Metric)</b>	3500
<b>Customs Number</b>	3926909988

**Content Unit(BMEcat)**

pcs.

**Weight (Metric)**

0.0031

**Weight (Imperial)**

0.007