


Specification Sheet

Part Number: 157-00361



Article Number

157-00361

Type

T50ROSLPM8SMSO25

Color

Brown (BN)

Features & Benefits

- Offset design positions bundles away from obstructions, heat or sources of abrasion.
- Low profile head allows mounts to stack, providing more mounting versatility from a single stud.
- Four-pawl, three-tooth design delivers outstanding stud retention to keep bundles secure.
- PA46 material option allows use in high-heat applications.

Quantity Per

carton

Product Description

This mount's offset design positions bundles away from obstructions, heat or sources of abrasion. It features a low-profile head, allowing multiple tie mounts to be stacked on a single bolt and providing space savings in tight areas. With their low insertion force and high extraction performance, HellermannTyton mounting ties offer the ideal combination of high-grade materials and superior design to suit the mounting and bundling needs of complex applications. Available in standard and high-heat material options.

Short Description	Offset Low-Profile M8 Stud Mount Tie, 7.5" Tie, 50lb Tensile Strength, PA46, Brown, 3000/pkg
Global Part Name	T50ROSLPM8SMSO25-PA46-BN
Minimum Tensile Strength (Imperial)	50.0
Minimum Tensile Strength (Metric)	223
Length L (Imperial)	8.9
Length L (Metric)	226.14
Offset Length(Imperial)	1.0
Offset Length(Metric)	25.5
Fixation Method	Stud Mount
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Width W (Imperial)	0.70
Width W (Metric)	17.75
Bundle Diameter Min (Imperial)	0.08
Bundle Diameter Min (Metric)	2.0

Bundle Diameter Max (Imperial)	1.97
Bundle Diameter Max (Metric)	50.0
Cable Ties	157-00361
Height H (Imperial)	0.25
Height H (Metric)	6.30
Mounting Hole Diameter D (Imperial)	0.31" x 0.05
Mounting Hole Diameter D (Metric)	M8 x 1.25
Stud Diameter (Metric)	8.0 mm
Stud Diameter (Imperial)	0.31
Material	Polyamide 4.6 (PA46)
Material Shortcut	PA46
Operating Temperature (Metric)	-40°F to +266°F (-40°C to +130°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Package Quantity(Imperial)	3000

Package Quantity (Metric) 3000

Customs Number 3926909988

Content Unit(BMEcat) pcs.

Weight (Metric) 0.0030

Weight (Imperial) 0.007