

Specification Sheet

Part Number: 157-00367



Article Number

157-00367

Type

T50ROSFT6SO12.5A

Color

Black (BK)

Features & Benefits

- Off-Set design allows bundles to sit off of mounting points to avoid friction against surrounding areas.
- Fir tree gives 3 to 1 extraction versus insertion force making them strong and easy to install.
- Friction tab inside of fir tree allows tie to sit in mount without falling out prior to installation.

Quantity Per

bag

Product Description

HellermannTyton's Off-Set Fir Tree Cable Tie and fixing offers a simple and easy to use method of bundling and fixing cables, the design of the fir tree ensures a positive and secure fixing into panels with thicknesses from .2" - .26" or threaded blind holes. The 'disc' on the top of the fir tree covers the hole and minimizes the ingress of water and dirt.

Short Description

1-Piece Cable Tie/Fir Tree Mount with Disc, 12.5mm Offset, 8.5"L, 6.1-7mm Hole, PA66HIRHS, Black, 3000/ctn

Global Part Name

T50ROSFT6SO12.5A-PA66HIRHS-BK

Minimum Tensile Strength (Imperial)

50.0

Minimum Tensile Strength (Metric)

222

Length L (Imperial)

8.5

Length L (Metric)

215.9

Offset Length(Imperial)

0.49

Offset Length(Metric)

12.5

Identification Plate Position

none

Releasable Closure

No

Width W (Imperial)

0.19

Width W (Metric)

5.1

Bundle Diameter Min (Imperial)

0.08

Bundle Diameter Min (Metric)

1.6

Bundle Diameter Max (Imperial)

1.97

Bundle Diameter Max (Metric)

50.0

Height H (Imperial)	0.87
Panel Thickness Min(Imperial)	0.02
Panel Thickness Max(Imperial)	0.26
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	6.65
Mounting Hole Diameter D (Imperial)	0.24 - 0.28 ";0.24 - 0.26
Mounting Hole Diameter D (Metric)	6.1 - 6.9 mm 6.35 mm (hexagonal)
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.28 ";0.26
Mounting Hole Diameter D Max (Metric)	6.9
Disc Diameter(Metric)	15.0
Disc Diameter (Imperial)	0.59
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
ROHS Complaint	Yes

Package Quantity(Imperial)

3000

Package Quantity (Metric)

3000

Customs Number

3926909988