

## Specification Sheet

Part Number: 157-00402



Article Number	157-00402
Type	WSR250
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none"><li>•Mount provides low insertion and high extraction forces which makes for a strong and easy installation.</li><li>•Tie utilizes a strong hinge between the stud mount and strap head to provide superior holding ability.</li><li>•Clamping rails increase grip on round bundles.</li><li>•Thinner strap provides increased flexibility for improved ergonomics.</li></ul>
Quantity Per	bag

### Product Description

The Wide Strap Stud Mount Cable Tie minimizes pinching on soft bundles and features a low profile head to provide compact bundling. A thinner strap provides increased flexibility for improved ergonomics. Available in various stud mount sizes, the wide strap tie utilizes a strong hinge between the stud mount and head to provide superior holding ability on a threaded stud.

<b>Short Description</b>	Wide Strap Cable Tie with .25" Stud Mount, 15.7" Long, .5" Wide, PA66HIRHSUV, Black, 300/Bag
<b>Global Part Name</b>	WSR250-PA66HIRHSUV-BK
<b>Minimum Tensile Strength (Imperial)</b>	120
<b>Minimum Tensile Strength (Metric)</b>	534
<b>Length L (Imperial)</b>	15.7
<b>Length L (Metric)</b>	398.8
<b>Fixation Method</b>	Weld Stud Fixing
<b>Identification Plate Position</b>	none
<b>Releasable Closure</b>	No
<b>Tie Closure</b>	plastic pawl
<b>Variant</b>	Inside Serrated
<b>Width W (Imperial)</b>	0.5
<b>Width W (Metric)</b>	12.7
<b>Bundle Diameter Min (Imperial)</b>	0.38
<b>Bundle Diameter Min (Metric)</b>	9.5
<b>Bundle Diameter Max (Imperial)</b>	4.1

**Bundle Diameter Max (Metric)**

104.1

**Stud Diameter (Metric)**

M6

**Stud Diameter (Imperial)**

1/4

**Material**

Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

**Material Shortcut**

PA66HIRHSUV

**Flammability**

UL 94 HB

**Operating Temperature (Metric)**

-40°F to +230°F (-40°C to +110°C)

**Reach Complaint(Article 33)**

Yes

**ROHS Complaint**

Yes

**Package Quantity(Imperial)**

300

**Package Quantity (Metric)**

300

**Customs Number**

3926909988

**Content Unit(BMEcat)**

pcs.

