

## Specification Sheet

Part Number: 157-00405



Wide Strap Cable Tie with .38" Stud Mount, 15.7" Long, .5" Wide, PA66HIRHSUV, Black, 300/Bag

|                     |   |
|---------------------|---|
| Article Number      | 157-00405   |
| Type                | WSR380  |
| Color               | Black (BK)  |
| Features & Benefits | <ul style="list-style-type: none"><li>•Mount provides low insertion and high extraction forces which makes for a strong and easy installation.</li><li>•Tie utilizes a strong hinge between the stud mount and strap head to provide superior holding ability.</li><li>•Clamping rails increase grip on round bundles.</li><li>•Thinner strap provides increased flexibility for improved ergonomics.</li></ul> |
| Quantity Per        | bag   |

### Product Description

The Wide Strap Stud Mount Cable Tie minimizes pinching on soft bundles and features a low profile head to provide compact bundling. A thinner strap provides increased flexibility for improved ergonomics. Available in various stud mount sizes, the wide strap tie utilizes a strong hinge between the stud mount and head to provide superior holding ability on a threaded stud.

|  |  |
|--|--|
| <b>Short Description</b>                   | Wide Strap Cable Tie with .38" Stud Mount, 15.7" Long, .5" Wide, PA66HIRHSUV, Black, 300/Bag |
| <b>Global Part Name</b>                    | WSR380-PA66HIRHSUV-BK  |
| <b>Minimum Tensile Strength (Imperial)</b> | 120.0  |
| <b>Minimum Tensile Strength (Metric)</b>   | 534  |
| <b>Length L (Imperial)</b>                 | 15.7   |
| <b>Length L (Metric)</b>                   | 398.8  |
| <b>Fixation Method</b>                     | Weld Stud Fixing   |
| <b>Identification Plate Position</b>       | none   |
| <b>Releasable Closure</b>                  | No   |
| <b>Tie Closure</b>                         | plastic pawl   |
| <b>Variant</b>                             | Inside Serrated  |
| <b>Width W (Imperial)</b>                  | 0.5  |
| <b>Width W (Metric)</b>                    | 12.7   |
| <b>Bundle Diameter Min (Imperial)</b>      | 0.38   |
| <b>Bundle Diameter Min (Metric)</b>        | 9.5  |
| <b>Bundle Diameter Max (Imperial)</b>      | 4.1  |

|                                     |       |
|-------------------------------------|-------|
| <b>Bundle Diameter Max (Metric)</b> | 104.1 |
|-------------------------------------|-------|

**Stud Diameter (Metric)** M10

|                                 |     |
|---------------------------------|-----|
| <b>Stud Diameter (Imperial)</b> | 3/8 |
|---------------------------------|-----|

|                 |  |
|-----------------|--|
| <b>Material</b> | Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV) |
|-----------------|--|

**Material Shortcut** PA66HIRHSUV

|                     |          |
|---------------------|----------|
| <b>Flammability</b> | UL 94 HB |
|---------------------|----------|

**Operating Temperature (Metric)** -40°F to +230°F (-40°C to +110°C)

|                       |     |
|-----------------------|-----|
| <b>ROHS Complaint</b> | Yes |
|-----------------------|-----|

|                                   |     |
|-----------------------------------|-----|
| <b>Package Quantity(Imperial)</b> | 300 |
|-----------------------------------|-----|

**Package Quantity (Metric)** 300

|                       |            |
|-----------------------|------------|
| <b>Customs Number</b> | 3926909988 |
|-----------------------|------------|

**Content Unit(BMEcat)** bag

