

## Specification Sheet

Part Number: 157-00415



Offset design positions bundles away from obstructions, heat or sources of abrasion.

Low profile head allows mounts to stack, providing more mounting versatility from a single stud.

Four-pawl, three-tooth design delivers outstanding stud retention to keep bundles secure.

Offset Low Profile M6 Stud Mount Tie, 25.5 mm Offset, 7.5"L, 50lb Tensile, PA66HIRHS, Black, 100/pkg

Article Number 157-00415

Type T50ROSLPM6SMSO25

Color Black (BK)

Quantity Per bag

**Product Description**

One-piece cable tie with stud mount features an offset design to position bundles away from obstructions, heat or sources of abrasion. It includes a low-profile head, allowing multiple tie mounts to be stacked on a single bolt and providing space savings in tight areas. With their low insertion force and high extraction performance, HellermannTyton mounting ties offer the ideal combination of high-grade materials and superior design to suit the mounting and bundling needs of complex applications. Available in standard and high-heat material options.

Short Description	Offset Low Profile M6 Stud Mount Tie, 25.5 mm Offset, 7.5"L, 50lb Tensile, PA66HIRHS, Black, 100/pkg
Global Part Name	T50ROSLPM6SMSO25-PA66HIRHSUV-BK
Minimum Tensile Strength (Imperial)	50.0
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	8.82
Length L (Metric)	224.0
Offset Length (Imperial)	1.0
Offset Length (Metric)	25.5
Fixation Method	Stud Mount
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Width W (Imperial)	0.19
Width W (Metric)	14.2
Bundle Diameter Min (Imperial)	0.08
Bundle Diameter Min (Metric)	2.0

Bundle Diameter Max (Imperial)	1.97
Bundle Diameter Max (Metric)	50.0
Height H (Imperial)	0.05
Height H (Metric)	1.35
Stud Diameter (Metric)	5.0 mm 6.0 mm
Stud Diameter (Imperial)	0.20 ", 0.24
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100

Customs Number

3926909988

## About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. ([www.hellermann.tyton.com](http://www.hellermann.tyton.com)).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)