

Specification Sheet

Part Number: 157-00421



Article Number

157-00421

Type

T50ROSFT5.6SO25R

Color

Black (BK)

Features & Benefits

- HIRHSUV solar fasteners provide excellent resistance to UV, chemical and moisture sensitive environments.
- Can be pre-installed while modules are still on the pallet.
- Barrel and offset head design reduces potential for abrasion and wear.
- First Solar vetted design.

Quantity Per

bag

Product Description

The Series 6 Solar Fir Tree Fastener is the easiest and fastest wire management solution on the market. It features a head design specifically tailored for First Solar Series 6 Modules. Entire fir tree passes through wire management hole to prevent unintended disengagement. Unique barrel head rests on module lip to relieve fir tree of downward forces. Offset keeps bundles the perfect distance from mounting hole, allowing nondestructive movement due to wind or tracker motion. The bent tail design allows quick and simple installations by hand.

Short Description	Series 6 Solar Fir Tree Fastener, 50lb Tensile Strength, PA66HIRHSUV, Black, 1000/bag
Global Part Name	T50ROSFT5.6SO25R-PA66HIRHSUV-BK
Minimum Tensile Strength (Imperial)	50.0
Minimum Tensile Strength (Metric)	222.0
Length L (Imperial)	8.0
Length L (Metric)	203.2
Offset Length(Imperial)	0.98
Offset Length(Metric)	25.0
Fixation Method	Fir Tree
Identification Plate Position	none
Releasable Closure	No
Variant	Outside Serrated
Width W (Imperial)	0.2
Width W (Metric)	5.08
Bundle Diameter Min (Imperial)	0.07
Bundle Diameter Min (Metric)	1.8

Bundle Diameter Max (Imperial)	1.97
Bundle Diameter Max (Metric)	50.0
Height H (Imperial)	0.41
Height H (Metric)	10.3
Diameter D (imperial)	0.36
Diameter D (metric)	9.04
Panel Thickness Min(Imperial)	0.19
Panel Thickness Max(Imperial)	0.17
Panel Thickness Min (Metric)	3.0
Panel Thickness Max (Metric)	4.25
Mounting Hole Diameter D (Imperial)	0.22
Mounting Hole Diameter D (Metric)	5.6 mm
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Operating Temperature (Metric)	-40°F to +230°F (-40°C to +110°C)

ROHS Complaint

Yes

Package Quantity(Imperial)

1000

Package Quantity (Metric)

1000

Customs Number

3926909988