

Specification Sheet

Part Number: 2P9C



Spiralwrap Protective Sheathing, .25" Diameter, PTFE, Natural, 100 ft/roll

Article Number	161-05047
Type	2P
Color	Natural (NA)
Features & Benefits	<ul style="list-style-type: none">• Sheathing allows flexible routing and lead-out of cables• The inner edges are beveled preventing damage to cables• Sheathing is reusable and resistant to most chemicals• Spiralwrap is U.L. Recognized
Quantity Per	reel
Product Description	HellermannTyton's Spiralwrap protective sheathing provides cable protection and flexible routing. Spiralwrap is wrapped around a group of cables to shield and organize.
Short Description	Spiralwrap Protective Sheathing, .25" Diameter, PTFE, Natural, 100 ft/roll

Global Part Name

2P-PTFE-NA

Length L (Imperial)

100.0

Length L (Metric)

30.48

Variant

Spiral Binding

Bundle Diameter Min (Imperial)

0.18

Bundle Diameter Min (Metric)

4.75

Bundle Diameter Max (Imperial)

2.0

Bundle Diameter Max (Metric)

50.8

Diameter D (imperial)

0.25

Diameter D (metric)

6.35

Nominal Diameter (Imperial)

1/4

Nominal Diameter (Metric)

6.35

Wall Thickness WT (Imperial)

.030

Wall Thickness WT (Metric)

0.76

Material

Polytetrafluoroethylene -Teflon (PTFE)

Material Shortcut

PTFE

Flammability

Non-Flammable

Halogen free

No

Operating Temperature (Metric)

-449°F to +500°F (-267°C to +260°C)

Reach Complaint(Article 33)

Yes

ROHS Complaint

Yes

UL Recognized (US)

Yes

Package Quantity(Imperial)

100

Package Quantity (Metric)

30.48

Customs Number

3926909988