

Specification Sheet

Part Number: 5N9C



Spiralwrap Protective Sheathing, 1" Diameter, PA6, Natural, 100 ft/roll

Article Number

161-05085

Type

5N

Color

Natural (NA)

Features & Benefits

- Sheathing allows flexible routing and lead-out of cables
- The inner edges are beveled preventing damage to cables
- Sheathing is reusable and resistant to most chemicals
- Spiralwrap is U.L. Recognized

Quantity Per

reel

Product Description

HellermannTyton's Spiralwrap protective sheathing provides cable protection and flexible routing. Spiralwrap is wrapped around a group of cables to shield and organize.

Short Description

Spiralwrap Protective Sheathing, 1" Diameter, PA6, Natural, 100 ft/roll

Global Part Name

5N-PA6-NA

Length L (Imperial)	100.0
Length L (Metric)	30.48
Variant	Spiral Binding
Bundle Diameter Min (Imperial)	1.0
Bundle Diameter Min (Metric)	25.4
Bundle Diameter Max (Imperial)	7.0
Bundle Diameter Max (Metric)	178.0
Diameter D (imperial)	1.0
Diameter D (metric)	25.4
Nominal Diameter (Imperial)	1
Nominal Diameter (Metric)	25.4
Wall Thickness WT (Imperial)	0.032
Wall Thickness WT (Metric)	0.81
Material	Polyamide 6 (PA6)
Material Shortcut	PA6

Flammability	Self-Extinguishing
Halogen free	Yes
Operating Temperature (Metric)	-40°F to +250°F (-40°C to +121°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
UL Recognized (US)	Yes
Package Quantity(Imperial)	100
Package Quantity (Metric)	30.48
Customs Number	3926909988