

Specification Sheet

Part Number: 161-64004



Article Number

161-64004

Type

HWCLIP16

Color

Black (BK)

Features & Benefits

- An innovative coupling system allows for an unlimited number of bundling combinations.
- Clips can be easily released and reused.
- Clips swivel freely which reduces mechanical stress and eliminates pinch points.
- High Impact Polyamide 6.6 material provides firm fit even in rugged conditions.
- Consists of acrylate adhesive with base of polyurethane foam allowing it to adhere firmly and easily to nearly any surface.

Quantity Per

bag

Product Description

The Helawrap cable management system is the flexible routing and protection solution for industrial, datacom and electrical applications. Clips can be joined to a base and another clip of any size. Different cable sizes can be bundled together, organized and protected flexibly and efficiently.

Short Description

Helawrap, Accessory Clip, HWCLIP16, 5/8" Dia, PA66HIRHS, Black, 50/pkg

Global Part Name

HWCLIP16-PA66HIRHS-BK

Fixation Method

Plug-in mounting

Diameter D (imperial)

0.59

Diameter D (metric)

15

Nominal Diameter (Imperial)

5/8

Nominal Diameter (Metric)

16.0

Material

Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)

Material Shortcut

PA66HIRHS

Flammability

UL 94 HB

Halogen free

Yes

Operating Temperature (Metric)

-40°F to +221°F (-40°C to +105°C)

Reach Complaint(Article 33)

Yes

ROHS Complaint

Yes

Package Quantity(Imperial)	50
Package Quantity (Metric)	50
Customs Number	3926909988
Content Unit(BMEcat)	pcs.
Weight (Metric)	0.14
Weight (Imperial)	0.3