

## Specification Sheet

Part Number: 161-64010



Helawrap, Accessory Clip, HWCLIP30, 1-1/4" Dia, PA66HIRHS, Black, 50/pkg

Article Number	161-64010
Type	HWCLIP30
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none"><li>•An innovative coupling system allows for an unlimited number of bundling combinations.</li><li>•Clips can be easily released and reused.</li><li>•Clips swivel freely which reduces mechanical stress and eliminates pinch points.</li><li>•High Impact Polyamide 6.6 material provides firm fit even in rugged conditions.</li><li>•Consists of acrylate adhesive with base of polyurethane foam allowing it to adhere firmly and easily to nearly any surface.</li></ul>
Quantity Per	bag

### Product Description

The Helawrap cable management system is the flexible routing and protection solution for industrial, datacom and electrical applications. Clips can be joined to a base and another clip of any size. Different cable sizes can be bundled together, organized and protected flexibly and efficiently.

**Short Description**

Helawrap, Accessory Clip, HWCLIP30, 1-1/4" Dia, PA66HIRHS, Black, 50/pkg

**Global Part Name**

HWCLIP30-PA66HIRHS-BK

**Fixation Method**

Plug-in mounting

**Diameter D (imperial)**

1.22

**Diameter D (metric)**

31

**Nominal Diameter (Imperial)**

1-1/4

**Nominal Diameter (Metric)**

30.0

**Material**

Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)

**Material Shortcut**

PA66HIRHS

**Flammability**

UL 94 HB

**Halogen free**

Yes

**Operating Temperature (Metric)**

-40°F to +221°F (-40°C to +105°C)

**Reach Complaint(Article 33)**

Yes

**ROHS Complaint**

Yes

**Package Quantity(Imperial)**

50

**Package Quantity (Metric)**

50

**Customs Number**

3926909988

**Content Unit(BMEcat)**

pcs.

**Weight (Metric)**

0.23

**Weight (Imperial)**

0.31