

## Specification Sheet

Part Number: 166-50172



HelaGuard Metal Locknuts, Metric Thread, 25mm, Nickel Plated Brass, Silver, 10/pkg

<b>Article Number</b>	166-50172
<b>Type</b>	ALNPB-M25
<b>Color</b>	Metal (ML)
<b>Features &amp; Benefits</b>	<ul style="list-style-type: none"><li>• Nickel plated brass thread ensures secure connection with brass plated fittings.</li><li>• Metric thread pattern works with metric thread fittings.</li></ul>
<b>Quantity Per</b>	bag
<b>Product Description</b>	Locknuts work with metric threaded fittings or knockout entries.
<b>Short Description</b>	HelaGuard Metal Locknuts, Metric Thread, 25mm, Nickel Plated Brass, Silver, 10/pkg
<b>Global Part Name</b>	ALNPB-M25-NPB-ML

<b>Variant</b>	Locknut
<b>Thickness T (Imperial)</b>	0.14
<b>Thickness T (Metric)</b>	3.5
<b>Nominal Diameter (Imperial)</b>	3/4
<b>Nominal Diameter (Metric)</b>	28
<b>Material</b>	Nickel Plated Brass (NPB)
<b>Material Shortcut</b>	NPB
<b>Halogen free</b>	Yes
<b>Operating Temperature (Metric)</b>	-58°F to +275°F (-50°C to +135°C)
<b>ROHS Complaint</b>	Yes
<b>Package Quantity(Imperial)</b>	10
<b>Package Quantity (Metric)</b>	10
<b>Customs Number</b>	7415338550

---

© 2019 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)