

Specification Sheet

Part Number: 166-50173



Article Number

166-50173

Type

ALNPB-M32

Color

Metal (ML)

Features & Benefits

- Nickel plated brass thread ensures secure connection with brass plated fittings.
- Metric thread pattern works with metric thread fittings.

Quantity Per

bag

Product Description

Locknuts work with metric threaded fittings or knockout entries.

Short Description

HelaGuard Metal Locknuts, Metric Thread, 32mm, Nickel Plated Brass, Silver, 2/pkg

Global Part Name

ALNPB-M32-NPB-ML

Variant	Locknut
Thickness T (Imperial)	0.18
Thickness T (Metric)	4.5
Nominal Diameter (Imperial)	1
Nominal Diameter (Metric)	34
Material	Nickel Plated Brass (NPB)
Material Shortcut	NPB
Halogen free	Yes
Operating Temperature (Metric)	-58°F to +275°F (-50°C to +135°C)
ROHS Complaint	Yes
Package Quantity(Imperial)	2
Package Quantity (Metric)	2
Customs Number	7415338550

